

## COMBINATION WRENCHES - METRIC | E113218



### Description

- ISO 691 - ISO 1711-1 - ISO 3318 - ISO 7738 - DIN 3113
- 12-point OGV® ring angled at 15°.
- Open end angled at 15° from handle axis.
- OGV® profile maximizing the contact surface with the nut for a longer lifetime.
- Forged in Chrome Vanadium steel.
- High chrome finish.

### Information

<b>EAN</b>	3258951132180
------------	---------------

<b>A [mm]</b>	23
---------------	----

<b>B [mm]</b>	48.7
---------------	------

<b>B1 [mm]</b>	33
----------------	----

<b>C [mm]</b>	8
---------------	---

<b>C1 [mm]</b>	11.9
----------------	------

<b>L [mm]</b>	260
---------------	-----

<b>Conditioning</b>	1
---------------------	---

<b>[g]</b>	235
------------	-----

