



fitted with

work equipment
connected load
power consumption
system of protection
class of protection
technology
usage
luminaire body
lamp cover
tubular sections

balance of articulation joints

weight (net)
mains lead

fastening

lens; dimensions
lens material
lens; diopters
add-on lens; dimensions

LED

Energy efficiency category A+
electronic plug-in ballast
100-240 V; 50/60 Hz
approx. 14 W
IP 20
II
continuously dimmable
multi-function switch
plastic, untreated, black
screen, milky, Polyamide
tubular aluminium section, anodized, aluminium coloured
anodised
spring
approx. 2.6 kg
approx. 3.6 m; mains plug
BS 1363
CEE 7/XVI
NEMA 1-15P
screw-down flange
Ø 160 mm
glass
3,5
not available



BS 1363



CEE 7/XVI



NEMA 1-15P

illuminance

distance: 15 cm

Em: 4002 lx
Emax: 6141 lx
Emin: 1377 lx

