

# PRODUCT DATA SHEET



**PRODUCT CODE:** 00710 **DESCRIPTION:** 17MM INSULATED OPEN ENDED GP SPANNER



**INSULATION MATERIAL:** NYLON THERMOPLASTIC

**LENGTH (MM):** 182

**METAL MATERIAL:** STEEL ALLOY 31CrV3

**WIDTH (MM):** 39

**SPECIFICATION:** IEC60900, CATEGORY 'C', VDE

**DEPTH (MM):** 19

**COUNTRY OF ORIGIN:** UNITED KINGDOM

**WEIGHT (G):** 128

**COMMODITY CODE:** 8204110000

**EAN:** 5052269007104



# The **ULTIMATE** in electrical and live line protection

ITL has over half a century's worth of experience producing insulated tools to the highest standard possible.

We manufacture unique, injection moulded, insulated tools from Nylon Thermoplastic. All our tools are 100% tested to IEC 60900, Category C and ASTM F1505.

*All over the world the professional uses ITL Insulated Tools:*

- We are the only company to insulate its tools with a unique injection moulded Nylon Thermoplastic recipe
- Tool and insulation bond as one
- Withstand extreme impact and abrasion
- Flame Retardant
- Stronger and harder than PVC coated tools
- 100% Production Tested –10,000 volts for 3 minutes submerged in water
- Accredited to IEC 60900:2018 – the International Standard for Live Line Working Tools
- Category “C” Impact Tested – for operation within greater temperature range **-40°F to +158°F -40°C to +70°C**
- Lifetime warranty on tool and insulation

