



Part Number : [936010177](#)

Product Description : Heavy-Duty Turned Crimp Contact for 16A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 1.50mm² (16 AWG), 100 per Bag

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Contacts

Engineering Number : 7300.6243.0



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Contacts
Series	93601
Description	Heavy-Duty Turned Crimp Contact for 16A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 1.50mm ² (16 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Name	Heavy-Duty Connectors
UPC	887191874951

Agency

CSA	256883
UL	E249674

Electrical

Current - Maximum per Contact	16.0A
-------------------------------	-------

Physical

Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	1.450/g
Number of Grooves	2
Packaging Type	Bag
Stripping Length	7.50mm
Wire Size (AWG)	16

Wire Size mm ²	1.50
---------------------------	------

Mates With / Use With

Mates with Part(s)

Description	Part Number
GWconnect Heavy-Duty Connectors and Accessories	<u>93601</u>

Use with Part(s)

Description	Part Number
Use With	S-AC, S-EC, S-EE, S-EEE, S-EHV,S-Q, S-QD, and S-M Inserts

This document was generated on Nov 06, 2025