

## NT 65/2 Ap

The NT 65/2 Ap is a powerful, 2-motor wet and dry vac for professional applications. The suction power remains nearly constant due to the efficient cleaning of the flat pleated filter by blasts of air.

### Standard accessories:

- Suction hose 4 m
- Metal suction tube
- 2 x 0.5 m
- Filter bag Paper
- Wet and dry floor tool 360 mm
- Crevice nozzle
- Drain hose (oil-resistant)
- Auto shutdown when max. level is reached
- Flat pleated filter Paper
- Bend
- Sturdy bumper
- Push handle
- Protection class II
- Castor with brake
- Maintenance-free suction turbines 2 piece



Order no.: 1.667-291.0

### Technical data

Air flow rate (l/s)	2 x 74
Vacuum (mbar/kPa)	254/25.4
Container capacity (l)	65
Max. power rating (W)	max. 2760
Standard nominal width (mm)	40
Cable length (m)	10
Sound pressure level (dB(A))	73
Container material	Plastic
Frequency (Hz)	50-60
Voltage (V)	220-240
Weight (kg)	20
Dimensions (L x W x H) (mm)	600x480x920

## Details

### Description

The NT 65/2 Ap is a powerful wet and dry vac with the ApClean system, which ensures constant high suction power and long working intervals. The vacuum features a compact turbine housing with integrated filter cover for easily removing the large flat pleated filter. It is effectively cleaned with the help of the semi-automatic ApClean filter cleaning system. This ensures constant high suction power, longer working intervals and a long service life of the filter. The NT 65/2 Ap features electronic fill level detection for wet vacuuming. It prevents the maximum permitted fill level from being exceeded. The problem-free disposal of vacuumed fluids is made possible by the attached oil-resistant drain hose. Accessories can be quickly and easily connected to the vacuum using the clip system. The unit features a hose storage device, an accessory holder and a large tray e.g. for tools. The required mobility of the NT 65/2 Ap is provided by two large fixed wheels and two guide rolls.

---

## Accessories

### Adapter (tube -> nozzle)

#### Adapter

From DN 40 to DN 61: Plastic adapter (electrically non-conductive). Suitable for NT vacuum cleaners.

Order no. 5.453-019.0



### Adapter for electric power tools, clip on, el.

#### Power tool adapter C 35, el.

3-way plastic adapter. For DN 26 to DN 36. For connecting power tools to an industrial C or C-DN 35 suction hose. Suitable for NT vacuum cleaners.

Order no. 5.453-042.0



#### Power tool adapter C 35, electrically conductive

Inside Ø 25.4 mm, outside Ø 34.6 mm/ 38 mm, electrically conductive. Only NT vacuums.

Order no. 5.453-048.0



#### Connecting sleeve for electric tool C 35, el.

Inner Ø 28.6 mm, outer Ø 37.3 mm/ 38.8 mm, el. Only NT-vacuums.

Order no. 5.453-049.0



#### Power tool adapter C 35, electrically conductive

Inside Ø 27 mm, outside Ø 36.5 mm/38.8 mm, electrically conductive. Only NT vacuums.

Order no. 5.453-050.0



#### Connecting sleeve for electric tool C 35, el.

Inner Ø 32 mm, outer Ø 39 mm, el. Only NT-vacuums.

Order no. 5.453-051.0



#### Connecting sleeve for electric tools C 35, el.

Inner Ø 28 mm, outer Ø 34 mm/ 38.8 mm, el. Only NT-vacuums.

Order no. 5.453-052.0



### Adapter for electric power tools, screwable

#### Power tool adapter, threaded, DN 35

3-way plastic adapter with fitting instructions. For DN 26 to DN 36. For connecting to an industrial DN 35 suction hose.

Order no. 5.453-016.0



#### Power tool adapter, threaded, DN 35

Inside Ø 28.6 mm, outside Ø 37.3/38.8 mm.

Order no. 5.453-026.0



## Adapter for electric power tools, screwable

### Power tool adapter, threaded, DN 35

Electrically conductive power tool adapter, threaded. Internal diameter: 32 mm. External diameter: 39 mm.



Order no. 6.902-059.0

### Power tool adapter, threaded, DN 35

2-way power tool adapter, threaded. For connecting to an industrial DN 35 suction hose. Internal diameter: 28 mm. External diameter: 34 mm and 38.8 mm Suitable for NT vacuum cleaners.



Order no. 6.902-095.0

## All-purpose brushes

### All-purpose brush

Natural bristles (ox hair), bristle element 120 x 45 mm.



Order no. 6.903-863.0

## All-purpose nozzles (wet/dry)

### All-purpose nozzle (wet/dry)

All-purpose plastic nozzle (DN 40) with 360 mm working width. With side rollers, brush strips (6.905-878.0) and squeegees (6.905-877.0). Only for NT vacuum cleaners.



Order no. 6.906-554.0

### All-purpose nozzle (wet/dry)

All-purpose aluminium nozzle with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.



Order no. 6.903-018.0

### All-purpose nozzle (wet/dry)

All-purpose aluminium nozzle (DN 40) with 450 mm working width. With height-adjustable side rollers, brush strips (6.903-065.0) and oil-resistant squeegees (6.906-146.0). Only for NT vacuum cleaners.



Order no. 6.906-383.0

### All-purpose nozzle (wet and dry), DN 35

All-purpose aluminium nozzle (DN 35) with 370 mm working width. With height-adjustable side rollers, brush strips (6.903-064.0) and oil-resistant squeegees (6.903-081.0). Only for NT vacuum cleaners.



Order no. 6.906-384.0

### All-purpose nozzle (wet/dry)

All-purpose plastic nozzle (DN 35) with 360 mm working width. With side rollers, brush strips (6.905-878.0) and squeegees (6.905-877.0). Only for NT vacuum cleaners.



Order no. 6.906-513.0

## Bend metal

### Bend, DN 35, metal

Robust, chromium-plated metal bend (DN 35), can be used instead of a plastic bend (with clip system adapter 5.407-112.0; C 35-DN 35, plastic, el.).



Order no. 6.900-519.0

### Bend, DN 40, metal

Robust, chromium-plated metal bend (DN 40), can be used instead of a plastic bend (with clip system adapter 5.407-111.0; C 40-DN 40, plastic, el.).



## Bend metal

Order no. 6.900-276.0

## Bend stainless

### Bend, stainless steel ID 35

Stainless steel and crooked, ID 35

Order no. 6.903-141.0



### Bend, stainless steel ID 40

Stainless steel and crooked, ID 40

Order no. 6.902-079.0



## Car cleaning nozzles

### Car vacuuming tool, DN 40

Angled, flat, plastic car vacuuming tool with about 90 mm working width. Only for NT vacuum cleaners.

Order no. 6.900-952.0



## Connecting sleeve C-DN (clip on taper), EL (electroconductive)

### C-DN 35 adapter

C 35 hose connector for DN 35 accessory, electrically conductive.

Order no. 5.407-112.0



### C 40 adapter

Electrically conductive adapter (C 40) with DN 35 connection for connecting DN 35 accessories to an industrial C 40 or C-DN 40 suction hose. Suitable for NT vacuum cleaners.

Order no. 5.407-109.0



### C-DN 40 adapter

C 40 hose connector for DN 40 accessory, electrically conductive.

Order no. 5.407-111.0



## Connecting sleeves

### Adapter, ID 32/35, with internal thread

Electrically non-conductive adapter with internal thread. For connecting two suction hoses without connectors. Suitable for DN 32 or DN 35.

Order no. 6.902-077.0



### Adapter, ID 40 with internal thread

Electrically non-conductive adapter with screw thread at both ends. For connecting 2 DN 40 suction hoses without connectors.

Order no. 6.900-286.0



### Connecting sleeve, ID 61, with female thread

For connecting 2 suction hoses, thread on both sides

Order no. 6.902-078.0



## Crevice nozzles

### Crevice tool

Plastic crevice tool (DN 40) for vacuuming in crevices and corners. Length: 290 mm.

Order no. 6.903-033.0



## Crevice nozzles

### Crevice tool

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 210 mm.

Order no. 6.900-385.0



### Crevice tool

Plastic crevice tool (DN 35) for vacuuming in crevices and corners. Length: 370 mm.

Order no. 6.900-922.0



### Crevice tool

Metal crevice tool (DN 40) for vacuuming in crevices and corners. Length: 400 mm.

Order no. 6.905-817.0



## Crevice tools

### Grout nozzle, synthetic

Grout nozzle, plastic, 370 mm

Order no. 6.900-222.0



### Grout nozzle, stainless steel

Grout nozzle, stainless steel, 400 mm

Order no. 6.900-926.0



## Extension hoses (Clip-system)

### Extension hose, C 40

2.5 m electrically non-conductive standard extension hose for all C-40 hoses with clip system.

Order no. 6.906-344.0



## Flat pleated filter (paper)

### Flat pleated filter

Paper flat pleated filter (BIA-(U,S,G,C) dust class M) suitable for NT 65/2 Eco, NT 65/2 Eco Tc, NT 65/2 Eco Me.

Order no. 6.904-283.0



## Flat pleated filter (PES)

### Flat filters (PES)

Flat filter (PES) - BIA-(U,S,G,C) dust class M: rotproof polyester fleece, ideal for wet use and abrasives. Standard for NT 72/2 Eco Tc.

Order no. 6.904-284.0



## Floor nozzles

### Floor nozzle cpl. 500 mm

Aluminium, oil-proof, 500 mm, with height-adjustable rollers, strips (6.903-067.0) and rubber lips (6.906-168.1)

Order no. 4.130-413.0



## HEPA filter for dust class H

### HEPA surface filter

HEPA surface filter - dust class H (H 14) - with glass-fibre layers increases filter capacity when vacuuming health-endangering and carcinogenic dust.

Order no. 6.904-364.0



## Membrane filter / fabric filter

### Membrane filter / fabric filter

Polyester needle fleece membrane/fabric filter - BIA-C -, washable up to 40°C, metal fibres for earthing. Suitable for virtually all industrial two-motor NT vacuum cleaners.



Order no. 6.904-282.0

## Miscellaneous

### Extension cable

Extension cable, 20 m, 3x1.5 mm<sup>2</sup>. With splash-proof earthing pin plug, strain relief and anti-kink sleeve.



Order no. 6.647-022.0

## Other accessories for T and NT

### Pre-separator

Complete container (80 litre) and lid (ID 61). For coarse dirt and fluids (without suction hose).



Order no. 3.864-010.0

### Lid for separator

For 6.902-051.0/4.070-111.0 and NT 802 I container



Order no. 4.063-132.0

### Drum separator

Metal, from DN 61 to 61, only for liquids.



Order no. 3.864-012.0

### Adapter ring for 200 l drum

Ring adapter for EURO steel drum (200 l) with lid but in connection with additional lid (separator) 4.063-132.0.



Order no. 6.902-051.0

## Paper filter (2 ply)

### Paper filter bags

5 3-ply, tear-resistant paper filter bags. BIA-(U, S, G, C) dust class M. For all NT 48/1, NT 65/2 Eco + Me and NT 72/2 Eco Tc models.



Order no. 6.904-285.0

## Pipe dusting nozzles

### Pipe dusting nozzle, ID 35

Plastic, pipe diameter 100 mm

Order no. 6.903-035.0



### Pipe dusting nozzle

Plastic, pipe diameter 200 mm

Order no. 6.903-036.0



## Plastic bend

### Plastic bend

Plastic bend (DN 40) with C-40 clip system, suitable for all NT models.

Order no. 5.031-904.0



## Plastic bend

### Plastic bend

Plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models (except NT Eco M and NT Eco H).

**Order no. 5.031-718.0**



### Plastic bend

Electrically conductive plastic bend (DN 35) with C-35 clip system. For all industrial single-motor NT 361 to NT 611 Eco models.

**Order no. 5.031-939.0**



### Plastic bend

Electrically conductive plastic bend (DN 40) with C-40 clip system, suitable for all NT vacuum cleaners.

**Order no. 5.032-427.0**



## Plastic sacks for dust-free disposal

### Plastic sacks for dust-free disposal

PE plastic sack.

**Order no. 6.900-698.0**



## Radiator brushes

### Radiator brush

Radiator brush is suitable for crevice tool 6.900-385.0 or 6.905-240.0.

**Order no. 6.903-034.0**



## Reducer (tube -> nozzle)

### Reducer

Reducer for accessory extension. Ideal for accessories with DN 35 connecting cone in combination with accessories with DN 40 connecting cone.

**Order no. 6.902-017.0**



### Reducer from ID 35 to 32

Reducer with internal connecting cone DN 32. Ideal for accessories from the industrial vacuum cleaner range in combination with industrial NT vacuum cleaners.

**Order no. 6.902-072.0**



## Reducing sleeves

### Reducer

Threaded reducer - from C-40 to DN 35. Suitable for NT vacuum cleaners.

**Order no. 5.407-108.0**



### Reducer

Reducer (C 40 to C 35) for connecting accessories with C-35 clip connection to suction hoses with C 40 clip system.

**Order no. 5.407-113.0**



## Repair kits

### Repair set, C 40

Repair set (C40) includes threaded hose adapters (without bayonet adapter) for industrial NT vacuum cleaners with clip system.

Order no. 2.639-873.0



### Repair kit, DN 61

Suction hose repair kit. Optional for all NT 65/2 and 72/2, NT 993 I, NT 802 I.

Order no. 2.862-038.0



## Rubber suction tools, nose 45°

### Rubber suction tools, nose 45°

45° rubber suction nozzle (DN 35), oil-resistant and suitable for vacuuming machines. Only for NT vacuum cleaners.

Order no. 6.902-104.0



### Rubber suction tools, nose 45°

45° rubber suction nozzle (DN 40), oil-resistant and suitable for vacuuming machines. Only for NT vacuum cleaners.

Order no. 6.902-105.0




## Rubber tool

### Rubber nozzle, ID 40

Rubber.

Order no. 4.763-057.0



## Set reducing / extension sleeves

### Set of reducers/adaptor sleeves

DN 40/35, DN 35/32 (tube -> nozzle), plastic.

Order no. 2.860-117.0



## Special filter bags, wet filter bags

### Special filter bags, wet filter bags

Approved for dust class L, general cleaning, wet and dry, tear-resistant.

Order no. 6.904-252.0



## Suction brushes

### Suction brush

Rotatable suction brush (DN 35) with natural bristles (cow hair). Bristle size 70x45 mm. Only CV and NT vacuum cleaners.

Order no. 6.903-862.0



## Suction hoses (Clip-system)

### Suction hose

4 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.

Order no. 6.906-321.0



## Suction hoses (Clip-system)

### Suction hose (clip system), C 40, 10 m

10 m standard suction hose without bend and adapter. With bayonet at vacuum end and C 40 clip connection at accessory end.

Order no. 6.906-279.0



### Suction hose

With bayonet and clip connection.

Order no. 6.906-714.0



### Suction hose

Electrically conductive, 4 m suction hose with bayonet and C 40 clip connection. Without bend and adapter.

Order no. 6.906-546.0



### Suction hose (Clip-system), C 40, 16 m

With bayonet and clip connection.

Order no. 6.906-635.0



### Suction hose (clip system), C 40, 10 m, el.

Suction hose with bayonet coupling, electrically conductive.

Order no. 6.906-877.0



## Suction hoses complete

### Suction hose, complete

4-m standard suction hose with DN 61 bayonet connector at the device end and DN 61 tapered connector at the accessory end.

Order no. 4.440-264.0



### Suction hose, complete

Industrial hose, PVC/elastomer with steel spiral, smooth inside

Order no. 4.440-328.0



### Suction hose, complete, ID 61, 10 m

10-m standard suction hose with DN 61 bayonet connector at the device end and DN 61 tapered connector at the accessory end.

Order no. 4.440-467.0



### Suction hose, complete, DN 61, 4 m, oil-resistant

Oil-resistant.

Order no. 4.440-613.0



### Suction hose, complete, DN 61, 10 m, oil-resistant

Oil-resistant.

Order no. 4.440-614.0



### Suction hose complete, ID 61, 4 m, el.

Electrically conductive.

Order no. 4.440-616.0



## Suction hoses complete

### Suction hose, complete

Electrically non-conductive 4.0m standard suction hose with bayonett at vacuum end and DN 40 cone at accessory end.

Order no. 4.440-263.0



### Suction hose, complete

Oil-resistant

Order no. 4.440-303.0



### Suction hose, complete

Electrically non-conductive 10.0m standard suction hose with bayonett at vacuum end and DN 40 cone at accessory end.


Order no. 4.440-463.0



### Suction hose complete

Electrically conductive, 10.0m, ID 40

Order no. 4.440-466.0



### Suction hose, complete, DN 40, 10 m, oil-resistant

Oil-resistant.

Order no. 4.440-612.0



## Suction hoses complete (Clip-system)

### Suction hose

4 m electrically non-conductive suction hose with bend, bayonet at vacuum end and C 40 clip connection at accessory end. Without module.

Order no. 4.440-678.0



### Suction hose, complete (clip system), C ID 40, 4 m

4 m electrically non-conductive suction hose with bend (C-DN 40) and module (4.060-474.0), bayonet at vacuum end and C 35 clip connection at accessory end.

Order no. 4.440-679.0



### Suction hose, complete (clip system), C DN-40, + PFC module, electrically conductive

With bend and module (4.060-533.0), electrically conductive.

Order no. 4.440-728.0



## Suction tubes metal

### Suction tube

Chromium-plated metal suction tube (DN 40, 1x0.5 m), standard for virtually all two-motor industrial vacuum cleaners. Optional for industrial single-motor NT vacuum cleaners with DN 40 suction hose.

Order no. 6.900-275.0



## Suction tubes metal

### Suction tube

Chromium-plated metal suction tube (DN 35, 1x0.5 m), standard for virtually all single-motor industrial NT vacuum cleaners.

Order no. 6.900-514.0



## Suction tubes stainless steel

### Suction tube, ID 40

Stainless steel suction tube (DN 40, 0.5 m) only suitable for NT vacuum cleaners.

Order no. 6.902-081.0



### Suction tube


Stainless steel suction tube (DN 40, 1.0 m) only suitable for NT vacuum cleaners.

Order no. 6.906-531.0



### Suction tube, DN 35

Order no. 6.902-154.0



## Target group specific vacuum cleaner accessory sets

### Professional cleaning kit ID 40

Individual parts: Suction hose 4 m (4.440-263.0), bend, metal (6.900-276.0), suction tube 2 x 0.5 m, metal (6.900-275.0), grout nozzle (6.903-033.0), floor nozzle with rollers (6.903-051.0).

Order no. 2.637-353.0



### Car cleaning kit

Target group-specific accessory nozzles in DN 35 for interior cleaning of vehicles, upholstery & fixtures.

Order no. 2.862-166.0



### Industry set

Target group-specific robust complete accessory set in DN 61 for vacuuming coarse dirt in industry, construction etc.

Order no. 2.637-355.0



### Chip cleaning kit

Target group-specific robust connection set in DN 61 for cleaning in conjunction with oil-resistant suction hose and rubber nozzle.

Order no. 2.640-760.0



### Bus kit

Accessory kit for vacuuming and cleaning buses, train compartments, etc., in combination with the recommended NT vacuum cleaner.

Order no. 2.640-560.0



## Tools for vacuuming smaller areas, cleaning machines

### 45° rubber suction nozzle

Angled 45°, for suction of machines, oil-resistant

Order no. 6.902-106.0



## Tools for vacuuming surfaces / cleaning machines

### Aluminium surface nozzle

Flat surface nozzle cpl. DN 51, 200 mm, aluminium with brush and stainless steel bumper

Order no. 4.130-415.0



### Metal scratcher and scraper nozzle

Scratcher and scraper tool DN 61, sheet metal, 117 mm

Order no. 6.903-360.0



## Y-adapter kit

### Y-adapter kit

Plastic distributor - suitable for NT vacuum cleaners.

Order no. 2.637-217.0

