

R5
PRO

EN

Datasheet

RS PRO Hermetically Sealed Enclosures

Stock number: 1920726




Product Details


Hermetic enclosure ideal for applications requiring protection against water ingress. Manufactured with polyurethane gasket that provides up to IP68 rating, it can be mounted on walls and other surfaces using mounting ears. Lid manufactured with recess for mambrane keypads and overlays. Threaded brass inserts ensures reliable assembly of the enclosure.

Features and Benefits

- Made of PC
- Available in light gray color
- Protection against liquids and solid objects: IP68 rating
- Shock protection level: IK07
- Supplied with silicon gasket and four screws
- Lid with recess for keypads and overlays
- Threaded brass inserts for reliable assembly.

rspro.com





Category	Hermetically Sealed Enclosures
Туре	Full with lug (U)
Material	PC
Variant	Hermetic with brass bushing (S TM)
Height	40.0 mm
Width	70.0 mm
Length	105.0 mm
Color	Lightgray (J)
Protection level	IP65/IP68
Shock protection level	IK07
Standards Met	RoHS Compliant
Accessories	Screw 3/20: 4.0 pcs
Certificate number	CE/032/18, Z/12/029118














Max PCB size



Dashed line shows outline of the mounting boss under PCB board Recommended mounting holes diameter ø4mm All dimensions are given within +/-0,5mm tolerance



