



Outlet filter, Extract: W: 191 mm, H: 191 mm, RAL 7035, IP55

Model		
product brand name		SIVACON
product designation		outlet filter
type of ventilation		ventilation
fan design withdrawable fan		No
design of the product EMC version		No
General technical data		
cutout width		191 mm
cutout height		191 mm
Protection class		
protection class IP		IP55
Appearance		
color		light grey
Product details		
product component fan		No
Mechanical Design		
height		323 mm
width		323 mm
depth		40 mm
installation location		Control cabinet...panels, door
fastening method		snap-on mounting
fastening method		
• 19-inch installation		No
• wall mounting		Yes
net weight		0.8 kg
material		plastic
ambient temperature during operation		
• minimum		-20 °C
• maximum		65 °C
Approvals Certificates		
General Product Approval		other
		Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6500-5GV67>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6500-5GV67>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6500-5GV67

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

