

Endress+Hauser Capacitance level switch FTC325-A1B11

Capacitance point level switch with intrinsically safe signal circuit for connection to a capacitance sensor.



Picture for reference only. Product appearance may vary based on configuration

Configuration of FTC325-A1B11:

Approval:	A	Non-hazardous area
Input; Housing:	1	2-wire PFM; 45mm, DIN Rail
Power Supply:	B	20-30VAC/20-60VDC
Switch Output:	1	1x SPDT level + 1x SPST alarm N.C. (normal closed)
Additional Option:	1	Basic version

Alternative part number: FTC325-A1B11