

HyFlex™

11-814

Second-skin design for high-precision handling



Multi Purpose



Light Duty

Boosts precision and productivity with exceptional second-skin comfort and tactile control

- **Second-Skin Design:** Engineered with AEROFIT™ Technology, an innovative, flexible foam nitrile coating that delivers improved tactility, sensitivity and a more comfortable, breathable glove feel.
- **Premium Comfort:** Our thinnest nitrile multi-purpose glove for all-day wear. Overwhelmingly preferred for precision handling*.
- **Proven Productivity:** Testing showed that users wearing HyFlex safety gloves with AEROFIT™ Technology completed precision tasks faster than when using comparable gloves on the market*.
- **Certified Skin Safety:** Dermatologically tested, free from harmful substances. Each pair is post-washed for clean, skin-safe wear.
- **Touchscreen Compatibility:** Enables seamless interaction with most touchscreen devices while keeping gloves on.



* Based on a survey of 52 glove wearers comparing Ansell gloves to the competitive gloves available on the market (May 2025); testing conducted with 11-844 gloves. Results may vary across other gloves in the series.

Industries

- Automotive
- Chemical

Applications

- Dry food handling & packaging
- Repair and maintenance

HyFlex™

11-814

Second-skin design for high-precision handling

Key Features

- ♦ **AEROFIT™ Coating:** up to 30% thinner* for exceptional tactility and control.
- ♦ **Highly Breathable Liner:** delivers premium comfort for all-day wear.
- ♦ **Productivity-Enhancing Design:** enables faster, more precise work.

* Versus standard Ansell glove with the same level of protection

Technologies



DMF free



Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3121A



1408033

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex™ 11-814	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Nylon, Spandex Cuff Style: Knitwrist	18	5, 6, 7, 8, 9, 10, 11, 12	180 - 252 mm / 7.09 - 9.92 in	Blue	• 12 pairs/paper band, 12 paper bands/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

