



Power Strip STRONG 5xT13 3m with Switch and Mounting Magnets black



Item No.: 207621135
EAN Code: 7611007122263

Description

Power Strip STRONG 5xT13 longitudinal, Td cable H05VV-F 3G1mm2, cable length 3m, T12 plug, reset switch (ON/OFF switch with resettable overcurrent protection), mounting magnets incl. adhesive metal mounting plates, cable winding device, black

Specifications

Type	Standard Power Strip
Brand	STEFFEN
Model	Strong
Number of Sockets	5
Socket Type	Type 13
Socket Colour	Anthracite
Socket Orientation	Longitudinal
Increased Touch Protection	No
Switch	Yes
Rated Current	10 A
Rated Voltage	230 V
Rated Frequency	50 - 60 Hz
Rated Power	2300 W
Cable Type	H05VV-F (Td)

Number of Conductors	3
Conductor Cross-Section	1 mm ²
Cable Length	3 m
Cable Colour	Black
Plug Type	Type 12
Mounting Option	Mounting Magnets with Adhesive Metal Mounting Plates, Hanging Eyelet
Main Material	Plastic
Halogen-Free	No
UV Resistance	No
Product Colour	Anthracite
Application	Indoor
K2 Suitable for Construction Sites	No
IP Rating	IP20
Operating Temperature Range	-5...+45 °C
Safety Features	Overcurrent Circuit Breaker
Additional Features	High-Impact-Resistant Housing
Product Height	290 mm
Product Width	100 mm
Product Depth	50 mm
Net Weight	0.490 Kg
Packaging	Shrink Wrap