






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE PER ECN-23-218419	25JUN2023	N.H	L.C
	A1	REVISED PER ECR-24-197900	29JAN2024	N.H	L.C

KEYING A SHOWN FOR 20 POSITION




- ⚠ MATERIAL: NYLON, UL94V-0, COLOR: SEE TABLE IN PAGE 2
2. THIS HOUSING ACCEPTS TERMINAL: 2371403-1
3. RECOMMENDED MATING PART: SEE TABLE IN PAGE 2
4. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDIITON




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BASAVARAJA D 31JUL2020		
		CHK CHEN LEO 31JUL2020		
DIMENSIONS:		APVD CHEN LEO 31JUL2020	NAME	
mm		PRODUCT SPEC	PLUG HOUSING, DUAL ROW, SGI 1.25	
		108-106451	SIZE	
		APPLICATION SPEC	CAGE CODE	
		114-106497	DRAWING NO	
		WEIGHT	RESTRICTED TO	
MATERIAL		CUSTOMER DRAWING	A 00779	
			SCALE 10:1	
			SHEET 1 OF 2	
			REV A1	

KEYING ILLUSTRATION




KEY A




KEY B

KEY A SHOWN FOR ALL POSITIONS


20 POSITION
2-2456588-0




22 POSITION
2-2456588-2



30 POSITION
3-2456588-0



40 POSITION
4-2456588-0



9-2456589-0	5.625	15.35	14.00	A	BLACK	20	9-2456588-0	
8-2456589-0	11.875	27.85	26.50	B	BLACK	40	8-2456588-0	
7-2456589-0	8.75	21.60	20.25			30	7-2456588-0	
6-2456589-0	5.625	15.35	14.00	A	NATURAL	20	6-2456588-0	
4-2456589-0	11.875	27.85	26.50			40	4-2456588-0	
3-2456589-0	8.75	21.60	20.25			30	3-2456588-0	
2-2456589-2	6.25	16.60	15.25			22	2-2456588-2	
2-2456589-0	5.625	15.35	14.00			20	2-2456588-0	
MATING HEADER	DIM "C"	DIM "B"	DIM "A"	KEYING	COLOR	POS	PART NO	REMARK

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±.030
1 PLC ±0.15
2 PLC ±.
3 PLC ±.
4 PLC ±.
ANGLES ±.
FINISH -

DWN: BASAVARAJA D A 31JUL2020
CHK: CHEN LEO 31JUL2020
APVD: CHEN LEO 31JUL2020

PRODUCT SPEC
108-106451

APPLICATION SPEC
114-106497

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
PLUG HOUSING, DUAL ROW, SGI 1.25

SIZE
A

CAGE CODE
00779

DRAWING NO
C=2456588

RESTRICTED TO
-

SCALE
8:1

SHEET
2

OF
2

REV
A1

4805 (3/13)