

5908VI/2T
Assortment of 232 tools for industrial maintenance in ABS thermoformed trays

Industrial maintenance

		art.
	059081105	5908VI/2T

- n. 5 **920ME**: 1/2" drive, socket drivers for hexagon screws $\bigcirc$ 5 - 6 - 8 - 10 - 12 mm
- n. 1 **920/21**: 1/2" drive extension bar 125 mm
- n. 1 **920/22**: 1/2" drive extension bar 255 mm
- n. 1 **920/25**: 1/2" drive universal joint
- n. 1 **920/42**: 1/2" drive sliding T-handle
- n. 1 **920/55**: 1/2" reversible ratchet 
- n. 19 **920A**: 1/2" square drive hexagon sockets $\bigcirc$ 10÷24 - 26 - 27 - 30 - 32 mm
- n. 16 **42**: combination wrenches 6÷21 mm
- n. 5 **42**: combination wrenches 22 - 24 - 27 - 30 - 32 mm
- n. 13 **900**: 1/4" hexagon sockets $\bigcirc$ 4÷14 mm
- n. 6 **900ME**: 1/4" socket drivers for hexagon screws $\bigcirc$ 2,5 - 3 - 4 - 5 - 6 - 8 mm
- n. 1 **900/20**: 1/4" drive extension bar 50 mm
- n. 1 **900/21**: 1/4" drive extension bar 150 mm
- n. 1 **900BG/30**: 1/4" drive spinner handle
- n. 1 **900/25**: 1/4" drive universal joint
- n. 1 **900/42**: 1/4" drive swivel T-handle
- n. 1 **900/55N**: 1/4" reversible ratchet 
- n. 6 **951**: T-handle wrenches with hexagon male ends $\bigcirc$ 2,5 - 3 - 4 - 5 - 6 - 8 mm
- n. 7 **90**: double ended offset ring wrenches 6x7-8x9-10x11-12x13-14x15-16x17-18x19 mm
- n. 5 **90**: double ended offset ring wrenches 20x22 - 21x23 - 24x26 - 25x28 - 27x29 mm
- n. 7 **1260**: screwdrivers for slotted head screws  2,5x50 - 3x75 - 3,5x100 - 4x125 - 5,5x100 - 5,5x150 - 6,5x150 mm
- n. 6 **1262**: screwdrivers for cross head Phillips® screws  PH0x60 - PH0x100 - PH1x80 - PH1x120 - PH2x100 - PH2x150 mm
- n. 3 **1260**: screwdrivers for slotted head screws  8x200 - 10x150 - 10x200 mm
- n. 2 **1260N**: screwdrivers for slotted head screws, extra-short series  4x30 - 6,5x30 mm
- n. 2 **1262**: screwdrivers for cross head Phillips® screws  PH3x150 - PH4x200 mm
- n. 2 **1262N**: screwdrivers for cross head Phillips® screws, extra - short series  PH1x30 - PH2x30 mm
- n. 2 **35**: flat chisels, ribbed type 100 - 200 mm
- n. 1 **1370**: engineer's hammer 300 g
- n. 1 **1390**: soft face hammer $\varnothing$ 35 mm
- n. 1 **1741**: riveting pliers 250 mm
- n. 100 **1741RV...K**: aluminium rivets 2,9x6 mm
- n. 100 **1741RV...K**: aluminium rivets 3,2x8 mm

