

## EMT (29X8)R


Order No.: 0817277

The figure shows the EMT (40x17)R version



Insert label, Roll, white, Unlabeled, Can be labeled with: Thermomark R, Thermomark X, Thermomark S, Mounting type: Insert, Cable diameter: 10-25 mm, Lettering field: 29 x 8 mm

### Commercial data

EAN	 4 046356 124218
Pack	1
Customs tariff	48211010
Gross weight in pieces	571.20 g
Country of Origin	DE
Catalog page information	Page 172 (CL2-2011)

### Product notes

WEEE/RoHS-compliant since:  
06/04/2006



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### General

Length (b)	29 mm
Width (a)	8 mm
Color	white
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C

Components	free from silicone and halogen
Material	Polyester
Number of individual labels	5400
Number of individual labels per row	3
RoHS compliant	Yes
Halogen-free	Yes
Silicone-free	Yes
Cadmium-free	Yes
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5145274 THERMOMARK X1.1
	5146231 THERMOMARK X1.2
	5145313 THERMOMARK S1
	5146257 THERMOMARK S1.1
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2006-02 + A1:2009-07
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Foil strength	175 µm

## Certificates

Certification

Certifications applied for:

Certification Ex:

---

**Accessories**

Item	Designation	Description
------	-------------	-------------

**General**

5145384	THERMOMARK-RIBBON 110	Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black
---------	-----------------------	--

---

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG, England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;