

## Product data sheet

### Characteristics

# 56K1SW332CK-GY

## 56 Series - Switch - Common Keylock - 3 Pole - 32A - 500V - grey



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

### Complementary

Switch function	3-pole
Poles description	3P
Actuator	Key
Control type	Rotary knob
Number of poles	3
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	32 A
Breaking capacity	32 kA
Motor M-rating AS3133	M200 at 500 V
Rotary handle padlocking	2 padlocks 8 mm
Marking	ON-OFF
Marking location	Marking on surface
Height	107 mm
Width	101 mm
Depth	112 mm
Net weight	0.667 kg
Targeted country	Australia

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

### Packing Units

Package 1 Weight	0.608 kg
------------------	----------

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>