

M12 FIW2F12/ M12 FIW2F38

M12 FUEL COMPACT IMPACT WRENCHES



- More Compact, greater access in Tight spaces with only 122mm in overall length.
- Light in weight at only 990g bare tool, best-in-class solution.
- 1/2" and 3/8" drive, producing up to 745Nm of maximum torque for applications.
- Single handed mode changes for quicker customization
- Auto-Shutoff applies no more than 20 Nm of torque for delicate fasteners

Battery System	M12
Max. Nut-busting Torque	745 Nm
No-Load Speed (mode 1-4)	0 – 930 / 2,100 / 3,000 / 1,300 RPM
Impact Rate (mode 1-3)	0 -1,500 / 3,000 / 3,300 IPM
Fastening Torque (mode 1-4)	271 / 406 / 542 / 20 Nm
Max. Bolt Diameter	M16
Anvil	1/2" and 3/8" Square w/ Friction Ring
Weight (Tool-Only)	990g
Recommended Battery	M12B..., M12 HB...