SMS24

24 Hour Mini Segment Timer Module

Features & Benefits

- Permanent ON/OFF or Timed Modes Via Slider Switch
- Spade Connector Terminals
- Segment ON/OFF Control



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	OEM
Operating Temperature	0°C to 40°C
Setting Type	Segment
Program Modes	24 Hour, Permanent ON/OFF or Timed
Switch type	Single Pole
Voltage Free Contacts	Normally Open, Normally Closed (Changeover)
Mounting Hole Centres (mm)	58 (Top/Bottom), 34 (Left/Right)
Number of Channels	1
Switch rating	16A Resistive, 4A Inductive




Shortest Switching Time	15 Minutes
Programmable Slots	48 ON 48 OFF (96 Segments)
Permanent ON Facility	Yes (Slider Switch)
Cable Entry(s)	Bottom Entry (Spade Connector)

General

Weight (g)	61
Height (mm)	67.5
Width (mm)	45
Depth (mm)	46
Body Construction	Polycarbonate
Product Colour	Black
EAN Number	5012483012925
Guarantee Period	3 Years

Line Diagrams





Data sheet **SMS24**

Time / OEM Modules

