

213.53.063 600 bar 2nd scale psi G1/4B back mount

Bourdon tube pressure gauges, liquid filled,

Item number:

Quantity: 1 pcs.

Order code: 213.53-C-BG560P-GB-A3ZZ-ZZZ 53 31ALZNZ2 ZA-ZZ1
DIAL-IAC1ZZZZRS001ZZ- 1Z1ZZ42ZZZ
LABEL-S61DE-##ZZZ

Overview: 213.53.063 600 bar 2nd scale psi G1/4B back mount
class 1.6
narrow panel ring, SS,rolled on,with mounting bracket
Window: plastic, clear
Case filling fluid: glycerine
single packing
stop-pin at zero
2nd scale red
EN 837-1 *Cl.1.6* *CE* LOGO: *RS* red RAL 3020
Label: WIKA UK customer: RS (Label yellow) "Made in Poland"
540-261
600 bar 63 mm G1/4B

Details: Bourdon tube pressure gauges, liquid filled,
stainless steel case, model 213.53.050/063
Model: 213.53
Specifications according to data sheet: PM 02.12
Measuring system: copper alloy
Case: stainless steel 1.4301
Case: Crimp ring case (version 53)
Nominal size: 063 mm
Scale range: 0...600 bar
2nd Scale or Special Scale: 2nd scale psi
Process connection: G 1/4 B
Connector location: back mount
Mounting flange/bracket: narrow panel ring, SS,rolled on,with mounting bracket
Accuracy class: class 1.6
Overpressure safe: standard
Case filling fluid: glycerine
Pointer: plastic, black (double division)
Window: plastic, clear
Packaging: single packing
Dial: plastic, white, with stop-pin
Dial description:
Pressure Gauge Standard: International (standard Europe)
color for 1.scale (outside): black
color for 2.scale (inside): red RAL 3020

Date: 22/01/2024



dial background: White
customer logo beginning with: RS
LOGO: *RS* red RAL 3020
stop pin on dial: at zero
norm-mark on dial: *EN 837-1*
accuracy class on dial: *Cl.1.6*
CE mark on dial: *CE*
description field 1 (ET1): 540-261
description field 2 (ET2): 600 bar 63 mm G1/4B