



Lighting **excellence**



@4liteuk



@4liteuk



@4lite





@4liteuk

Pavia

Pavia IP54 Bulkhead White
Code: 4L2/3221

Application Commercial, Kitchen / Dining, Living



Product Features

- Innovative installation bracket design for quick, secure, and hassle-free mounting.
- Multi-wattage flexibility – easily adjust power and brightness to suit different applications.
- High IK rating – robust and impact resistant, ideal for busy communal areas.
- Multiple options available – a versatile solution to meet varied project requirements.
- IP54 rated – reliable protection against dust and splashes, perfect for bathrooms and corridors.
- Multi-CCT selectable – choose the right colour temperature for maximum versatility.
- Retrofit ready – designed to replace existing fittings with minimal disruption.

Technical Information

Wattage	12W/22W
Lumens Delivered	1500lm - 2500lm (4000K)
Lm/W	120lm/W
Beam Angle	110
CRI	80
CCT	3000K/4000K/6500K
Input	220-240V
Operating Temp	-10°C - 35°C
SDCM	6
UGR	24
Energy efficiency class	F
Product Weight without Packaging	0.999 kg

Technical Information

Light Source	LED
Colour / Finish	White
IP Rating	IP54
Class Protection	2
Internal / External	Internal
Mounting Option	Surface
Lumen Depreciation	L90 54,000h
Warranty (Years)	4
CE Mark	Yes
Diameter	304 mm