




Part Number : [639023400](#)

Product Description : FineAdjust Applicator for Mega-Fit Female Terminals

Series Number : 207127

Status : Active

Product Category : Applicators and Crimp Modules



Documents & Resources

Tooling Specifications

[ATS-639023400-001.pdf](#)

[TM-638000029-001.pdf](#)

[TM-638004900-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for Mega-Fit Female Terminals
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust
Tool Type	Applicator
UPC	887191147888
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

Physical

Net Weight	4672.002/g
------------	------------

Mates With / Use With

Use with Part(s)

Description	Part Number
TM-2000 Universal Press	<u>638008300</u>
TM-2000 Universal Press (Europe 220V)	<u>638008400</u>
TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10 AWG	<u>638017200</u>
TM-3000 Universal Crimp Press, 220AC 50/60Hz, Used for product up to 10 AWG	<u>638017300</u>
TM-4000 Universal Crimp Press, 240AC 50/60Hz, Used for product up to 4 AWG	<u>638017600</u>
Use With	Most Industry Standard Presses or Wire Process Machines

Applicable Parts

Description	Part Number
Mega-Fit Crimp Terminal, Female, Tin (Sn) Plating, 12 AWG, Reel	<u>768230322</u>
Mega-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 12 AWG, Reel	<u>1720630312</u>
Mega-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 12 AWG, Reel	<u>1720631312</u>