

Metal drill bits HSS PointTeQ

PRODUCT PROPERTIES					ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Shank diameter (d) mm	Diameter (D) Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
5.1	52	86	5.1	-	P1h	10	1	3165140907286	2 608 577 219
5.2	52	86	5.2	-	P1h	10	1	3165140907293	2 608 577 220
5.3	52	86	5.3	-	P1h	10	1	3165140907309	2 608 577 221
5.4	57	93	5.4	-	P1h	10	1	3165140907316	2 608 577 222
5.5	57	93	5.5	-	P1h	10	1	3165140907323	2 608 577 223
5.6	57	93	5.6	-	P1h	10	1	3165140907330	2 608 577 224
5.7	57	93	5.7	-	P1h	10	1	3165140907347	2 608 577 225
5.8	57	93	5.8	-	P1h	10	1	3165140907354	2 608 577 226
5.9	57	93	5.9	-	P1h	10	1	3165140907361	2 608 577 227
6	57	93	6	-	P1h	10	1	3165140907378	2 608 577 228
6.1	63	101	6.1	-	P1h	10	1	3165140907385	2 608 577 229
6.2	63	101	6.2	-	P1h	10	1	3165140907392	2 608 577 230
6.3	63	101	6.3	-	P1h	10	1	3165140907408	2 608 577 231
6.4	63	101	6.4	-	P1h	10	1	3165140907415	2 608 577 232
6.5	63	101	6.5	-	P1h	10	1	3165140907422	2 608 577 233
6.6	63	101	6.6	-	P1h	10	1	3165140907439	2 608 577 234
6.7	63	101	6.7	-	P1h	10	1	3165140907446	2 608 577 235
6.8	69	109	6.8	-	P1h	10	1	3165140907453	2 608 577 236
6.9	69	109	6.9	-	P1h	10	1	3165140907460	2 608 577 237
7	69	109	7	-	P1h	10	1	3165140907477	2 608 577 238
7.1	69	109	7.1	-	P1h	10	1	3165140907484	2 608 577 239
7.2	69	109	7.2	-	P1h	10	1	3165140907491	2 608 577 240
7.3	69	109	7.3	-	P1h	10	1	3165140907507	2 608 577 241
7.4	69	109	7.4	-	P1h	10	1	3165140907514	2 608 577 242
7.5	69	109	7.5	-	P1h	10	1	3165140907521	2 608 577 243
7.6	75	117	7.6	-	P1h	10	1	3165140907538	2 608 577 244
7.7	75	117	7.7	-	P1h	10	1	3165140907545	2 608 577 245
7.8	75	117	7.8	-	P1h	10	1	3165140907552	2 608 577 246
7.9	75	117	7.9	-	P1h	10	1	3165140907569	2 608 577 247
8	75	117	8	-	P1h	10	1	3165140907576	2 608 577 248
8.1	75	117	8.1	-	P1h	10	1	3165140907583	2 608 577 249
8.2	75	117	8.2	-	P1h	10	1	3165140907590	2 608 577 250
8.3	75	117	8.3	-	P1h	10	1	3165140907606	2 608 577 251
8.4	75	117	8.4	-	P1h	10	1	3165140907613	2 608 577 252
8.5	75	117	8.5	-	P1h	10	1	3165140907620	2 608 577 253
8.6	81	125	8.6	-	P1h	10	1	3165140907637	2 608 577 254
8.7	81	125	8.7	-	P1h	10	1	3165140907644	2 608 577 255
8.8	81	125	8.8	-	P1h	10	1	3165140907651	2 608 577 256
8.9	81	125	8.9	-	P1h	10	1	3165140907668	2 608 577 257
9	81	125	9	-	P1h	10	1	3165140907675	2 608 577 258
9.1	81	125	9.1	-	P1h	10	1	3165140907682	2 608 577 259
9.2	81	125	9.2	-	P1h	10	1	3165140907699	2 608 577 260
9.3	81	125	9.3	-	P1h	10	1	3165140907705	2 608 577 261
9.4	81	125	9.4	-	P1h	10	1	3165140907712	2 608 577 262
9.5	81	125	9.5	-	P1h	10	1	3165140907729	2 608 577 263
9.6	87	133	9.6	-	P1h	10	1	3165140907736	2 608 577 264
9.7	87	133	9.7	-	P1h	10	1	3165140907743	2 608 577 265
9.8	87	133	9.8	-	P1h	10	1	3165140907750	2 608 577 266
9.9	87	133	9.9	-	P1h	10	1	3165140907767	2 608 577 267
10	87	133	10	-	P1h	10	1	3165140907774	2 608 577 268
-	22.5	48	-	1/16	P2a	10	1	3165140908252	2 608 577 316
-	25.5	51	-	5/64	P2a	10	1	3165140908269	2 608 577 317
-	32.5	57	-	3/32	P2a	10	1	3165140908276	2 608 577 318
-	39	68	-	7/64	P2a	10	1	3165140908283	2 608 577 319
-	42	71	-	1/8	P2a	10	1	3165140908290	2 608 577 320
-	45	74	-	9/64	P2a	10	1	3165140908306	2 608 577 321