


# ITS 3106 (A) and ITS 3106 (R) ITS 4106 (A) and ITS 4106 (R) Straight Cylindrical Plug Assembly

with Backshell for the Attachment of Additional Accessories



### Application Notes:

- 1. Straight plug with backshell for the attachment of strain relief cable clamps.
- Connector/Backshell Class "A" (non-environmental)—Not supplied with wire sealing grommet; Class "R" (environmental)—Supplied with backshell and grommet.
- 3. Standard materials configuration consists of aluminum alloy. For platings, see TABLE II finish options.
- 4. Standard contact material consists of copper alloy with silver plating or gold plating.
- 5. A broad range of other front and rear connector accessories are available. See our website and/or contact the factory for complete information.
- Standard insert material is synthetic rubber. Add "FR" prefix to front of part number to specify fire resistant inserts.

```
© 2010 Glenair, Inc.
```

U.S. CAGE Code 06324

Printed in U.S.A.

Series ITS

## ITS 3106 (A) and ITS 3106 (R) ITS 4106 (A) and ITS 4106 (R) **Straight Cylindrical Plug Assembly** with Backshell for the Attachment of Additional Accessories



	L	ØQ		
Shell Size	Max.	±0.2	V Thread	
10 SL	44.0	22.6	0.6250 - 24UNEF	
14 S	46.4	29.0	0.7500 - 20UNEF	
16 S	46.4	31.6	0.8750 - 20UNEF	
16	57.8	31.6	0.8750 - 20UNEF	
18	57.8	36.2	1.0000 - 20UNEF	
20	58.1	39.8	1.1875 - 18UNEF	
22	58.1	43.0	1.1875 - 18UNEF	
24	59.7	46.4	1.4375 - 18UNEF	
28	66.2	53.0	1.4375 - 18UNEF	
32	71.3	60.0	1.7500 - 18UNS	
36	76.8	66.2	2.0000 - 18UNS	
40	76.8	72.3	2.2500 - 16UN	

### **TABLE I: DIMENSIONS**

#### **TABLE II: MODIFICATION CODES**

CONTACT OPTIONS		ACCESSORY OPTIONS		
Sym	Description	N1	Connector with IT 3057 A cable clamp	
B0	Connector Less Contacts	N2	Connector with long backshell	
B1	Connector with Gold Plated Contacts	N5	Connector with IT 3057 C cable clamp	
Omit for standard version (Silver plated)		N12	Connector with IT 3057 A cable clamp	
FINISH OPTIONS			and IT 3420 neoprene sleeve	
Sym Description and RoHS compliant (*)			Omit for standard version	
F2	Bright Nickel Plating (*)			
F6	Black Electrodeposited Paint (*)			
F7	Black Zn-Co Plating (*)			
F8	Olive Drab Zn-Co Plating			
F11	Electroless Nickel (*)			
	Omit for standard version (Cadmium Olive Drab Finish)			

U.S. CAGE Code 06324