

MID BLAST

Foundry boot



Foundry standard marking

Technology



open cell
PU footbed

Dual Density Rubber sole



Features

Standard	ENISO 20349:2017
Category	S3 HI CI HRO SRC Fe
Code	HM2005WSI
Product type	Foundry boot
Colour	Black
Size range	UK sizes 5 - 13 EU 39 - 48
Weight	1070gr
Upper	Full Grain Barton Print Buffalo Leather with higher Chrome Content (1.8 – 2.0mm)
Inner lining	Moisture wicking textile to vamp only
Safety features	Stainless Steel Toe Cap, resistant to 200J Stainless Steel Protective Midsole – Min. 1100N

Additional features

Flame resistant stitching.
Foundry standard markings.

Soling technology

Lightweight Injected Flame Retardant Dual Density Rubber/Rubber, Flexible soling system with antistatic properties, shock absorption, heat resistance to 300°C and SRC rated slip resistance.

Insole technology

Moisture wicking, breathable and washable
Open Cell PU Footbed

