



FASTIN-FASTON Connection System
**Straight Receptacles with Locking Lance
for Single & Multiple Connections
6.3 mm (.250 Series)**

A - Without Dimple

B - With Dimple

Style	Tab Thickness (mm)	Wire Range (mm²)	Insulation Diameter (mm)	Material and Finish	Dimensions (mm)			Part Number
					W	L	E	
A	0.8	0.3-0.8	2.2-3.2	Brass	7.4	19.2	7.8	280095-1
				Brass-Tin Plated				280095-2
		0.5-1.0	1.4-2.3	Brass-Tin Plated				160928-2
				Ph. Bronze				160928-3
				Ph. Bronze-Tin Plated				160928-4
				Brass				5-160526-6
		0.5-1.5	2.3-3.3	Brass-Tin Plated				5-160526-7
				Brass-Silver Plated				6-160526-1
				Ph. Bronze-Tin Plated				5-160526-9
				Brass				42100-1
		0.8-2.5	3.1-4.1	Brass-Tin Plated				42100-2
				Brass				6-160448-0
				Brass-Tin Plated				6-160448-5
				Brass-Silver Plated				6-160448-6
		1.0-2.5	3.4-5.1	Ph. Bronze				6-160448-1
				Ph. Bronze-Tin Plated				6-160448-2
				Ph. Bronze-Silver Plated				6-160448-3
				Brass-Tin Plated				160927-2
		1.0-2.5	2.1-3.1	Ph. Bronze				160927-3
				Ph. Bronze-Tin Plated				160927-4
				Brass				180351-1
				Brass-Tin Plated				180351-2
		4.0-6.0	3.4-5.1	Brass-Silver Plated				180351-6
				Ph. Bronze				180351-3
				Ph. Bronze-Tin Plated				180351-5
				Brass-Tin Plated				160860-2
		0.5-1.0	1.4-2.3	Ph. Bronze				160860-3
				Ph. Bronze-Tin Plated				160860-4
		0.5-1.0	2.0-3.3	Brass				160870-1
				Ph. Bronze				160870-3
		0.5-1.5	2.3-3.3	Brass				5-160558-1
				Brass-Tin Plated				5-160558-2
				Ph. Bronze-Tin Plated				5-160558-9
				Ph. Bronze-Silver Plated				6-160558-0
		0.8-2.5	3.1-4.1	Brass				42281-1
				Brass-Tin Plated				42281-2
				Brass-Tin Plated				5-160446-5
				Brass-Silver Plated				5-160446-6
B	0.8	1.0-2.5	3.1-4.1	Ph. Bronze	7.4	19.2	7.8	5-160446-1
				Ph. Bronze-Tin Plated				5-160446-2
				Ph. Bronze-Silver Plated				5-160446-8
				Brass-Tin Plated				160917-2
		1.0-2.5	2.1-3.1	Ph. Bronze				160917-3
				Ph. Bronze-Tin Plated				160917-4
		2.5-4.0	3.3-4.5	Ph. Bronze				160913-3
				Ph. Bronze-Tin Plated				160913-4
		4.0-6.0	4.0-5.2	Brass-Tin Plated				160914-2
				Ph. Bronze				160914-3
				Ph. Bronze-Tin Plated				160914-4
				Ph. Bronze-Tin Plated				160914-4

Related to DIN 46340

Type B suggested for connections with less than 4 contacts