

8015
Wire rope clips, American type, steel body, hot-dip galvanized

c€

dimensioni EN 13411-5
TECHNICAL DATA

- traceability code

LABORATORY TESTS

- chemical analysis
- torque test

AVAILABLE CERTIFICATES

- Technical product specifications
- Test report UNI EN10204 type 2.2
- Manufacturer's Certificate UNI EN13411-5
- CE Declaration of Conformity



	art.	Ø mm	Ø "	NxT	Nm
080150808	8015 8	8	5/16	3x133	40,7
080150810	8015 10	9-10	3/8	3x165	61
080150813	8015 13	11-13	1/2	3x292	88
080150816	8015 16	14-16	5/8	3x305	129
080150820	8015 20	18-20	3/4	4x460	176
080150822	8015 22	22	7/8	4x480	305
080150826	8015 26	24-26	1	5x660	305
080150830	8015 30	28-30	1-1/8	6x860	305