

Eaton 168837

Catalog Number: 168837

Eaton Distribution parts. Phase busbar, N, 16qmm, fork connector, 1m, 2MU

General specifications



Product Name	Catalog Number
Eaton Distribution parts	168837
EAN	Product Length/Depth
4015081653188	1000 mm
Product Height	Product Width
35 mm	7 mm
Product Weight	Compliances
0.26 kg	RoHS conform

Product specifications

Used with

BB-EV

Busbar

Type

BB-EV

Busbar

Features

Insulated

Can be cut to size

Accessory/spare part type

Busbar for TVSS

Busbar for combined residual current/power circuit breaker

Busbar for miniature circuit breaker

Busbar for residual current circuit breakers

Electric connection type

Fork

Rated surge voltage

4.5 KV

Rated uninterrupted current (Iu)

80 A

Suitable for number of devices

0

Application

Switchgear for industrial and advanced commercial applications

Number of poles

Two-pole

Color

Other

Rated short-time withstand current (Icw)

0 kA

Cross section

16 mm²

Number of modular spacings

2

Number of phases

1

Resources

Drawings

[eaton-dimensions-mas-zv7-80a.jpg](#)

Wiring diagrams

[eaton-wiring-diagram-versch.jpg](#)

Pitch dimensions

36 mm

Rated operational voltage (Ue) - max

690 V

Rated conditional short-circuit current (Iq)

0 kA

Functions

Busbar

Suitable for

Devices with N-busbar



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)