

Fan XGT®

CF003G

40Vmax, ø 450 mm

Model CF003G is a cordless portable fan powered by 40Vmax XGT®/18V LXT Li-Ion battery and AC (through AC adapter).

The main features and benefits are: Compatible with three power sources: 40Vmax XGT® Li-Ion battery, 18V LXT® Li-Ion battery and AC (through AC adapter). Variable speed control dial switch enables user to adjust to a desired air flow volume (air speed). Portability can be enhanced by mounting the appliance onto a MAKPAC cart. Fan cover can be removed for cleaning simply by removing screw. Accessory case on the front of the appliance can be used for storing the AC adapter.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Max. Air Velocity	1,6 - 5,0 m/s
Air volume	120 m³/min
Continuous Use XGT® 40V Max / 4.0 Ah	115 min
Diameter (D)	450 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Tool weight with battery	8,49 - 9,7 kg
Product net weight	7,8 kg
Product Dimensions (L x W x H):	343 x 633 x 770 mm
Angle range horizontal	180 °
Angle range vertical	135 °
Automatic rotational angle (left / right)	60 / 90 / 120 °

User benefits

- Easily removable fan cover for convenient clean-up
- Designed to withstand harsh job site environments
- Strong enough to create a comfortable work environment under hot weather conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.com



Related products

Other

User manual

Parts drawing