

Type : Air & Water Hose

Type No. : 2007

Application : Air / Water

S

Description :

Black compressed-air hose for pneumatic equipment, tools, compressors, etc. Also suitable for water. Fits standard claw couplings used in the building sector.

Working Temperature : -30°C to +80°C

Std. Branding : CODAN 2007 - AIR HOSE diM - 20
BAR WP - sn.

Reinforcement : Polyester

Inside : SBR Colour : Black
Outside : SBR Colour : Black
Standards : ISO 188/ISO 2398

Data

Inside dia. mm	Outside dia. mm	Working Pressure BAR	Burst Pressure BAR	Bend Radius mm	Weight g/m	Product number
10.0	18.0	20	60	70	300	2007010
13.0	23.0	20	60	91	450	2007013
16.0	26.0	20	60	112	550	2007016
19.0	30.0	20	60	133	650	2007019
25.0	36.0	20	60	175	900	2007025

Illustration

