



sealing cap M12 for ET200clean, plastic version, hygienic seal, for degree of protection IP69K, 10 units per packing unit

General information			
Product description	M12 sealing cap, hygiene design		
Suitability for use	necessary accessories for use of ET 200clean in food production in hygiene areas		
Mechanical data			
Torque, max.	1 N·m		
Degree and class of protection			
IP degree of protection	IP65/67/69K		
Ambient conditions			
Ambient temperature during assembly, min.	-30 °C		
Ambient temperature during assembly, max.	60 °C		
Ambient temperature during operation			
• min.	-30 °C		
• max.	55 °C		
connection method			
Design of thread	M12x1		
Mechanics/material			
Material			
• Plastic	Yes; + silicone seal		
Material property			
• Halogen-free	Yes		
• Silicone-free	No		
Weights			
Weight, approx.	2 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	9	EC002584
	ETIM	8	EC002584
ETIM	7	EC002584	

