

8020A
Thimbles, Italian light type, galvanized
AVAILABLE CERTIFICATES

- Technical product specifications
- Test report UNI EN10204 type 2.2



	art.	Ø mm	F mm	B mm	D mm
080200503	8020A 2-3	2-3	1,0	20	18
080200504	8020A 4	4	1,2	23	19
080200505	8020A 5	5	1,2	24	23
080200506	8020A 6	6	1,2	27	28
080200508	8020A 8	8	1,4	33	32
080200510	8020A 10	10	1,8	41	38
080200512	8020A 12	12	2,2	44	45
080200514	8020A 14	14	2,2	52	49
080200516	8020A 16	16	3,0	58	58
080200518	8020A 18	18	3,7	64	68
080200520	8020A 20	20	3,7	73	74
080200522	8020A 22	22	3,7	83	79
080200525	8020A 25	24	3,7	93	88
080200703	8020S 2-3	2-3	0,8	150	
080200704	8020S 4	4	1,0	150	
080200705	8020S 5	5	1,0	100	
080200706	8020S 6	6	1,0	100	
080200708	8020S 8	8	1,2	50	
080200710	8020S 10	10	1,5	30	