

### Main

Range of product	Odace
Product or component type	LED
Product specific application	Replacement lamp
Type of packing	Paint cover




### Complementary

Light source colour	Blue
Product destination	Fixing frame
Fixing mode	Clip-in
Colour tint	Grey (RAL 7030)
Temperature rise	25 °C
Current consumption	5 mA
Number of cables	2
Material	PC (polycarbonate) GF10 FR: casing
Embedding depth	12.5 mm
Net weight	0.0027 kg

### Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Environmental characteristic	Alcohol Petrol Window-cleaning fluid UV resistant Acetone Oil Bleach Liquid soap

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>