


PC-Board layout
view component side
thickness 1,6 mm




Coding style table	
	Style A: For connectors 6 poles
	Style B: For connectors 10 and 14 poles
	Style C: For connectors from 16 to 64 poles

-Technical information available on a separate document ref: DS 09181100001
-Full range of P/N's and dimensions shown on page 2/2

	All rights reserved Department EC PD - FR	Created by DOUGE	Inspected by BAGDIKIAN	Standardisation HOFFMANN	Date 2014-05-16	State Final Release	Ref. Sub.
	HARTING Electronics GmbH D-32339 Espelkamp	Title SEK 18 male right angled low profile		Doc-Key / ECM-Nr. 100565919/UGD/001/A 50000068837		Rev. A	Page 1/2
All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.				
Type TB	Number 09185XXX323						

		Performance Level			Dimensions				
		PL3	PL2	S4					
		Part Number	Part Number	Part Number	Insulator Color	A Max	B	E	
A	B	06	0918 506 7323	0918 506 6323	0918 506 5323	Grey	15,4	12,78	2,54 x 2 = 5,08
		10	0918 510 7323	0918 510 6323	0918 510 5323		20,5	17,86	2,54 x 4 = 10,16
		14	0918 514 7323	0918 514 6323	0918 514 5323		25,6	22,94	2,54 x 6 = 15,24
		16	0918 516 7323	0918 516 6323	0918 516 5323		28,1	25,48	2,54 x 7 = 17,78
		20	0918 520 7323	0918 520 6323	0918 520 5323		33,2	30,56	2,54 x 9 = 22,86
		26	0918 526 7323	0918 526 6323	0918 526 5323		40,8	38,18	2,54 x 12 = 30,48
		30	0918 530 7323	0918 530 6323	0918 530 5323		45,9	43,26	2,54 x 14 = 35,56
		34	0918 534 7323	0918 534 6323	0918 534 5323		51,0	48,34	2,54 x 16 = 40,64
		40	0918 540 7323	0918 540 6323	0918 540 5323		58,6	55,96	2,54 x 19 = 48,26
		50	0918 550 7323	0918 550 6323	0918 550 5323		71,5	68,66	2,54 x 24 = 60,96
		60	0918 560 7323	0918 560 6323	0918 560 5323		84,2	81,36	2,54 x 29 = 73,66
		64	0918 564 7323	0918 564 6323	0918 564 5323		89,3	86,44	2,54 x 31 = 78,74
C	D	06	0918 506 7323 001	0918 506 6323 001	0918 506 5323 001	Black	15,4	12,78	2,54 x 2 = 5,08
		10	0918 510 7323 001	0918 510 6323 001	0918 510 5323 001		20,5	17,86	2,54 x 4 = 10,16
		14	0918 514 7323 001	0918 514 6323 001	0918 514 5323 001		25,6	22,94	2,54 x 6 = 15,24
		16	0918 516 7323 001	0918 516 6323 001	0918 516 5323 001		28,1	25,48	2,54 x 7 = 17,78
		20	0918 520 7323 001	0918 520 6323 001	0918 520 5323 001		33,2	30,56	2,54 x 9 = 22,86
		26	0918 526 7323 001	0918 526 6323 001	0918 526 5323 001		40,8	38,18	2,54 x 12 = 30,48
		30	0918 530 7323 001	0918 530 6323 001	0918 530 5323 001		45,9	43,26	2,54 x 14 = 35,56
		34	0918 534 7323 001	0918 534 6323 001	0918 534 5323 001		51,0	48,34	2,54 x 16 = 40,64
		40	0918 540 7323 001	0918 540 6323 001	0918 540 5323 001		58,6	55,96	2,54 x 19 = 48,26
		50	0918 550 7323 001	0918 550 6323 001	0918 550 5323 001		71,5	68,66	2,54 x 24 = 60,96
		60	0918 560 7323 001	0918 560 6323 001	0918 560 5323 001		84,2	81,36	2,54 x 29 = 73,66
		64	0918 564 7323 001	0918 564 6323 001	0918 564 5323 001		89,3	86,44	2,54 x 31 = 78,74

	All rights reserved Department EC PD - FR	All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.	Ref. Sub.
		Created by DOUGE	Inspected by BAGDIKIAN	Standardisation HOFFMANN	Date 2014-05-16	State Final Release
HARTING Electronics GmbH D-32339 Espelkamp		Title SEK 18 male right angled low profile				Doc-Key / ECM-Nr. 100565919/UGD/001/A 50000068837
		Type TB	Number 09185XXX323		Rev. A	Page 2/2