

Parvalux Electric Motors Ltd

PARVALUX

490-492 Wallisdown Road, Bournemouth, Dorset, BH11 8PU
 Tel.: +44 (0) 1202 512575, Fax: +44 (0) 1202 530885
 Company Number: 446422 VAT Number: 927328705

Part specification for part **PM4-0087/CONT**

Motor Specifications

Enclosure	TENC	Footed	FEET	Voltage	24
AC/DC	DC	Rated Speed RPM	3000	Duty Rating	CONT
Winding Code	GX	Spindle	43000	Phase	
6 Lead		Lead Length		Thermal Trip	
Wiring Diagram	77 + 101	Field Code		Terminal Box	NO
Motor Rotation	REV	Rated Output Watts	90	T/Box Position	
Hertz		Capacitor		Current/Amps	5.2
Motor Test Number	PM 28				

Gearbox Specifications

Primary Ratio	30	Secondary Ratio		Gearbox Rotation	REV
Gear Shaft Position	3YZ	Gearbox RPM	100	Gear Test Number	P14102
Gearbox Torque	4.2	Shaft	46940	Gear Material	COMPOSITE

Top Level

Brake	NO	Encoder		Tachometer	
Paint	BLUE	Machine Code		Insulation	F
CSA	CE	Specification	718694	Drawing	
Assembly Type	TOP LEVEL	Thermal Class			