

Features

- Ceramic Fuse
- 10X38 mm cartridge size
- RoHS compliant
- Class of Operations: AR

RS PRO Cartridge Fuses

RS Stock No.: 0199249



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

*Fuses for semiconductor protection.
Class of operation aR (full semiconductor protection).
For the protection of high-quality devices and components, such as semiconductor contactors, electronic relays (solid state), converters with fuses at the input and in DC intermediate circuits, UPS systems, and soft-start devices for motors.*

Electrical Specifications

Current Rating	1A
Voltage Rating	690V
Fuse Type	aR Cylindrical
Fuse Size	10x38 mm
Testing Standard	IEC 60269-4, GB/T 13539.4, UL 248-13
Body Material	Ceramic
Fuse Speed	aR

Electrical characteristics

% of CURRENT RATING		BLOWING TIME	
		250mA-5A	6A-32A
400%	Max.	1 seconds	10 seconds
	Min.	3 ms	10 ms
1000%	Max.	20 ms	30 ms

Approvals

Compliance/Certifications	CCC, VDE, cURus   OF  US, RoHS
Standards	IEC 60269-4, GB/T 13539.4, UL 248-13



Due to our policy of continuous product improvement, we reserve the right to discontinue or change product specifications or designs at any time without notice and without incurring obligations. You should always contact us for the most up-to-date information on our products