

Label sheet, DIN A4 - BMKL 27X27 SR CUS - 0824256

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Label sheet, DIN A4, can be ordered: Sheet, silver, labeled according to customer specifications, Mounting type: Adhesive, Lettering field: 27 x 27 mm



The figure shows a version of the article

Why buy this product

- These labels have been specially developed for laser printers
- The unperforated SK U ... sheets are available for custom label designs
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers



Key commercial data

| | |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc |
| GTIN |  4 046356 351317 |
| Weight per Piece (excluding packing) | 9.0 g |
| Custom tariff number | 39199000 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------|-------|
| Length (b) | 27 mm |
| Width (a) | 27 mm |

Ambient conditions

| | |
|---------------------------------|--------------------------------|
| Ambient temperature (operation) | -20 °C ... 120 °C (Min.) |
| Ambient temperature (assembly) | > 5 °C |
| Recommended storage conditions | 22 °C / 50 % relative humidity |

General

| | |
|-------|--------|
| Color | silver |
|-------|--------|

Label sheet, DIN A4 - BMKL 27X27 SR CUS - 0824256

Technical data

General

| | |
|---------------------------------------------------------------------|-------------------------------------|
| Base element material | Polyester |
| Components | Silicone-free |
| Material | Polyester |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 54 |
| Number of individual labels per row | 6 |
| Adhesive | Acrylic |
| Printability | Office printing systems |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Wipe resistance test result | Test passed |
| Salt spray test specification | DIN EN ISO 9227:2012-09 |
| Salt spray testing result | Test passed |
| Alternating condensation climate with SO2 test specification | Following DIN 50018:2013-05 |
| Climate level | AHT 1.0 S |
| Cycles | 2 |
| Condensation test result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result | Test passed |
| Foil strength | 46 µm |
| Adhesive strength | 29 µm |
| Marking mounting type | Adhesive |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

Label sheet, DIN A4 - BMKL 27X27 SR CUS - 0824256

Classifications

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |