

Product data sheet

179 N W-7/314

EAN-No. 4000896250493



314-pieces · 7 Drawers total



- More storage space than preceding model
- 6 flat drawers, loading capacity 25 kg, 81 mm high
1 high heavy-duty drawer, loading capacity 40 kg, 166 mm high
- Complete with 314-piece tool assortment in Safety-Insert-System soft foam insert
- 30 mm wood multiplex birch work surface, oiled, replaceable
- Including nine-fold adjustable intermediary tray and fixed mounted door
- Cable aperture on rear panel allows, for example battery-powered devices to be charged when the door is locked
- Complete welded construction of the entire body for tough daily workshop use
- Additional square perforation for tool holder, e.g. HAZET 112-230
- Optimised, yielding edge protection on all four corners with real impact protection thanks to internal damping concept
- Flexible vice assembly (front, right, left) e.g. HAZET 2175N as per drilling templates
- **Chassis:**
 - Large wheels with high loading capacity (Ø 125 mm) with precision ball-bearing and dual ball race in the swivel bearing, easy manoeuvrability even under high dynamic load
 - 2 swivel castors with dual brake:
 - Braked castors prevent rolling away
 - Braked swivel bearings prevent the swivel castors from turning, e.g. on inclined surfaces
 - Protective ring prevents dirt and threads from getting in
 - Elastic castors enable smooth movement
- **Locking concept:**
 - Mutual drawer locking for minimum tilting risk
 - Lock located in the centre (central locking and cylinder lock) closes the door and drawers at the same time
 - Only one key for locking the door and drawers at the same time (Included in delivery: 2 keys)
 - 180° rotation, prevents the key from breaking off
 - 100 % sliding-out with ball-bearing telescopic rails – self-closing
 - Lockable storage compartment with 2 storage surfaces
- 2 storage spaces in the storage compartment, top: 15 kg / bottom: 35 kg
- Total loading capacity (dynamic): 750 kg
- Loading capacity (static): 1000 kg
- Worktop: Wood multiplex birch, replaceable
- Colour: HAZET blue
- Tool trolley Made in Germany
- Dimensions: 1150 mm x 600 mm x 964 mm
- Net weight: 120 kg
- Drawers, flat: 6 x 81 x 522 x 398 mm
- Drawers, high: 1 x 166 x 522 x 398 mm
- (Drawer) size for plastic drawer insert: 3/3+

Product data sheet

179 N W-7/314

EAN-No. 4000896250493



163-526/41N

•, •, •, •



811 • •

0.4 x 2.5 • 0.5 x 3 • 0.8 x 4 •
1 x 5.5 • 1.2 x 6.5



811PH • •

PH0 • PH1 • PH2



811T • •

T10 • T15 • T20 • T25 •
T27 • T30



811K • •

0.6 x 3.5 • 1 x 5.5



811KPH • •

PH1 • PH2



811S • •

0.8 x 4.5 • 1 x 5.5 • 1.2 x 7



811SPH • •


PH1 • PH2 • PH3



2105LG/9H • •



2116LG/8H • •



163-609/61

•, •, •, •, •, •



760-2

986 • • • 1/2

4 • 5 • 6 • 7 • 8 • 9 • 10 •
12 • 14 • 17 • 19 • 22



986SL • • • 1/2

4 • 5 • 6 • 7 • 8 • 9 • 10 •
11 • 12 • 14

990 • • • 1/2

M5 • M6 • M8 • M10 • M12 •
M14 • M16 • M18

990LG • • • 1/2

M6 • M8 • M9 • M10 • M12 •
M14

991 • • • 1/2

M6 • M7 • M8 • M9 • M10 •
M12 • M14

992 • • • 1/2

T20 • T25 • T27 • T30 •
T40 • T45 • T50 • T55 • T60

992SLG • • • 1/2

T30 • T40 • T45 • T50 • T55

1850M-22



1841MB-33

1802M-22



2128N-1