



Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP unmanaged switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP
Port Ethernet	100BASE-FX - 1 port(s) fiber optic 10BASE-T/100BASE-TX - 4 port(s) copper cable
Maximum number of switches in cascade	Unlimited

Complementary

Integrated connection type	Duplex SC fiber optic Shielded RJ45 copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E for copper cable Multimode optical fiber for fiber optic
Attenuation	11 dB 62.2/125 μ m 8 dB 50/125 μ m
Ethernet service	Automatic negotiation of 10/100 Mbit/s and duplex mode Auto MDI/MDX Automatic change of polarity Storage and re-routing of received data
[Us] rated supply voltage	24 V
Supply voltage limits	9.6...32 V DC SELV
Power consumption in W	3.9 W
Electrical connection	Removable connector 3 ways power supply
Marking	CE
Local signalling	1 LED fiber port state and activity 1 LED power supply 1 LED per channel copper port activity 1 LED per channel 10 or 100 Mbit/s data rate
Ethernet cabling system	TF switches
Width	25 mm

Height	114 mm
Depth	79 mm
Product weight	0.12 kg

Environment

Ambient air temperature for operation	0...60 °C
Relative humidity	> 0...95 % without condensation
IP degree of protection	IP30
Standards	CSA C22.2 No 142 CUL 508
Product certifications	CE

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0744 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available End of Life Information
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------

Power Wiring

