



Rear panel IP55, W: 1200 mm

Model	
product brand name	SIVACON S4
product designation	Rear panel
design of the surface	powdered
design of the product EMC version	No
Protection class	
protection class IP	IP55
Appearance	
RAL color number	sonstige
color	RAL 7035
Product details	
product component	
• cable entry	No
• lock	No
Mechanical Design	
height	2 000 mm
width	1 200 mm
depth	25 mm
net weight	30.3 kg
material	sheet-steel
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

Environment

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2420-2BA01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2420-2BA01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2420-2BA01

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/13/2025 

