

611828100

Aluminium Enclosure Standard unpainted 180 x 280 x 101 mm

Aluminium Enclosure Standard unpainted
180 x 280 x 101 mm

Declaration of Conformity

Technical Drawing | 3D Data | Assignmentplan | Terminal mounting

Technical data

Height	180 mm
Width	280 mm
Depth	101 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AlSi 12 (Fe)
Colour	Aluminium, unpainted
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
Temperature min.	-30 °C
Temperature max.	90 °C
Seal material	CR-(Chloropren)
Flame spread, sideways	HL 3
Rate of heat dispersion	HL 3
Smoke gas concentration	HL 3

Commercial data

Country of origin	DE
Order unit	1 Piece
Customs tariff number	85369095
Weight	2.67 kg
GTIN	4250157900289

ETIM Classification

ETIM 8	EC000058

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



100110300
Mounting plate for 01.182810



100220010
Hinges internal / steel



100270010
Hinges external / grey



100311020
Outer bracket fastening set M6



100614570
DIN rail 35/7,5 for 01.182810



100620090
Earth rail for 01.232811