



Datasheet

RS PRO 19mm Metal Pushbutton Switches 24V, Red LED



RS Article No.	Body type	Button type	Contact Configuration	Operating type	Light type	LED color	LED voltage	Terminal Plating
111-5817	Stainless	High	1NO 1NC	Lock	Ring (Fixed)	Green	110V	Silver







SPECIFICATIONS:

25/04/2016

Rating: Ith 5A/250VAC resistive load 3A/250VACContact Resistance: 50mΩ max. @1A 12VDC (initial value)Insulation Resistance: 1,000mΩ min. at 500VDCDielectric Strength: 2,000V RMS @sea levelOperation Temperature: -20°C to 55°CMechanical Life: 1,000,000 cycles; self-lock 500,000 cycles.Electrical Life: 50,000 make-and-break cycles at full loadTorque: 5~14NmPanel Thickness: 10mm (Ø19.20mm)Operation Pressure: 1Pole 2.5±1N / 2Poles 3.5±1NTravel: about 3.2mmIngress Protection: IP67, IK10

Materials Bushing: Stainless Steel/ Nickel plated brass/ Aluminum alloy Base: PBT (UL 94-V0), PC (UL 94-V2) Actuator: PC (UL94-V2); Stainless Steel/ Nickel plated brass/ Aluminum alloy Inner Assembly: POM/PA66 SPRING: Spring steel Sealing: Silicone O-Ring: Silicone Terminal/ Contact: Cooper, Silver plated Hex Nut: Nickel plated brass