

Logitech Wireless Mouse M185

Brand : Logitech

Product code: 910-002240

Product name : Wireless Mouse M185

M185 Wireless Mouse

Logitech Wireless Mouse M185. Form factor: Ambidextrous. Movement detection technology: Optical, Device interface: RF Wireless, Movement resolution: 1000 DPI, Buttons type: Pressed buttons, Buttons quantity: 3, Scroll type: Wheel. Power source: Batteries. Product colour: Red



Mouse		System requirements	
Number of scroll wheels	1	Linux operating systems supported	✓
Purpose *	Office	Other operating systems supported	ChromeOS
Device interface *	RF Wireless	Weight & dimensions	
Movement detection technology *	Optical	Width	60 mm
Movement resolution *	1000 DPI	Depth	99 mm
Buttons type	Pressed buttons	Height	39 mm
Scroll type *	Wheel	Weight	75.2 g
Scroll	✓	Receiver width	1.44 cm
Buttons quantity *	3	Receiver depth	6.1 mm
Recommended usage	Laptop	Receiver height	1.87 cm
Frequency band	2.4 GHz	Receiver weight	1.8 g
Design		Packaging data	
Form factor *	Ambidextrous	Package width	87 mm
Product colour *	Red	Package depth	126 mm
Surface coloration	Monochromatic	Package height	118.5 mm
Ergonomics		Package weight	142.4 g
Wireless range	10 m	Packaging content	
Plug and Play	✓	Receiver included	✓
Power		Wireless receiver interface	USB Type-A
Power source *	Batteries	Receiver type	Nano receiver
Number of batteries supported	1	Batteries included	✓
Battery type	AA	User guide	✓
Battery technology	Alkaline	Other features	
Battery capacity	2000 mAh	USB required	✓
Service life of battery	12 month(s)	Logistics data	
		Harmonized System (HS) code	84716070

System requirements

Windows operating systems supported 

Mac operating systems supported MacOS

Logistics data

Master (outer) case width	101 mm
Master (outer) case length	362 mm
Master (outer) case height	259 mm
Master (outer) case gross weight	1.76 kg



5099206028869

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 23-SEP-2025. Prints or copies of Information are only valid on the printed Publication date