



SPECIFICATION

| | | |
|--------------------------------|----------|---------------------|
| CONTACT FORM/STYLE | | A/Open |
| SWITCHING VOLTAGE | Max. Vac | 100 |
| SWITCHING CURRENT | Max. A | 0.25 |
| SWITCHING CAPACITY (RESISTIVE) | Max. VA | 5 |
| CONTACT RESISTANCE | Max. mΩ | 200 |
| SWITCHING DISTANCE | Min. mm | 8.0 |
| OPERATING TEMPERATURE | Deg. °C | -20° + 70° |
| STORAGE TEMPERATURE | Deg. °C | -25° + 70° |
| CASE MATERIAL | | Black Polypropylene |

RECTANGULAR MAGNETIC PROXIMITY SWITCHES

PART NUMBER
S1365

| Rev. No. | Revision Note | Date | Signature |
|----------|---------------|---------|-----------|
| A | FIRST ISSUE | 10.6.97 | P.P. |



BS5750/ISO 9000
Reg. No. FM 21080