



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [SCHRACK Relay Package XT](#)



AC Relays(8)



General Purpose Power Relays(12)

Customers Also Bought



TE Part #4-2213818-5
6X6 ILL TACT THT 260GF HI SOFT
ORANGE




TE Part #1879353-4
RR02 5% 5K6 AMMO



TE Part #5-1393239-1
RT21L024




TE Part #1622694-1
LR2 1% 16K



TE Part #1586863-4
4P VAL-U-LOK R/A HDR GW




TE Part #1-2213819-0
6X6 ILL TACT SMT 100GF HI PURE
GREEN



TE Part #3-1623714-3
FCB4 6K8 5% HP



TE Part #1-2273089-4
M12 x 1.0 angled socket pigt A



TE Part #7-2176379-4
RQ 0805 619R 0.1% 10PPM 5K RL



TE Part #3-2176379-0
RQ 0805 215R 0.1% 10PPM 5K RL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1415540-8_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1415540-8_A.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_4-1415540-8_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Relay Package XT](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English