





# PRODUCT DATASHEET

Datasheet creation date: 2025/07/08 2:25 (UTC)



## 51106

### Single-Direction Thrust Ball Bearings



#### Boundary Dimensions

d	30	mm	Bore diameter
D	47	mm	Outside diameter
T,T3	11	mm	Height
r (min.)	0.6	mm	Chamfer dimension

#### Basic Load Ratings

Ca	20600	N	Basic dynamic load rating
C0a	42000	N	Basic static load rating

#### Speeds

Grease	4300	min-1	Grease lubrication
Oil (Oil-bath)	6700	min-1	Oil-bath lubrication

#### Dimensions

d1	47	mm	Outside diameter shaft washer
D1	32	mm	Inner diameter housing washer

#### Abutment and Fillet Dimensions

da (min.)	40	mm	Diameter of shaft abutment
Da (max.)	37	mm	Diameter of housing abutment
ra (max.)	0.6	mm	Radius of shaft or housing fillet

#### Mass

Mass approx.	0.064	kg	Mass approx.
--------------	-------	----	--------------