



UC113 Longsleeve Poloshirt




Specification

- 50% Polyester 50% Cotton
- Long Sleeve
- Reactive Dyed
- Knitted Raised Collar & Plain Cuffs
- Taped Neck
- Side Vents with Extended Back
- Washable at 60 Degrees
- 3 Self Coloured Button Placket

Colours



Sizes



Size Guide

Your body measurement	XS	S	M	L	XL	2XL	3XL	4XL
Chest to fit (Inch)	36-38	38-40	40-42	42-44	44-46	46-48	50-52	52-54
Chest to fit (cm)	91-96	96-101	101-107	107-112	112-117	117-122	122-132	132 - 137

International conversion								
Austria, Switzerland, German, Netherlands, Sweden	44	46	48	50	52	54	56	58
Belgium, Spain, France, Portugal	36-38	38-40	40-42	42-44	44-46	46-48	48-50	50-52

	INCH	INCH	INCH	INCH	INCH	INCH	INCH	INCH
UC113 Long sleeve Poloshirt garment Measurements	XS	S	M	L	XL	XXL	3XL	4XL
CHEST 1/2 measurement (1" BELOW ARMHOLE)	19.0	20.0	21.0	23.0	24.0	25.0	27.0	29.0
LENGTH (NECK POINT ON SHOULDER TO HEM) FRONT	25.0	27.0	28.0	29.0	30.0	30.0	31.0	32.0
LENGTH (NECK POINT ON SHOULDER TO HEM) BACK	26.0	28.0	29.0	30.0	31.0	31.0	32.0	33.0

	CM	CM	CM	CM	CM	CM	CM	CM
UC113 Long sleeve Poloshirt garment Measurements	XS	S	M	L	XL	XXL	3XL	4XL
CHEST 1/2 measurement (2.5cm BELOW ARMHOLE)	48.0	51.0	53.0	58.5	61.0	63.5	68.5	73.5
LENGTH (NECK POINT ON SHOULDER TO HEM) FRONT	63.5	68.5	71.0	73.5	76.0	76.0	78.5	81.0

LENGTH (NECK POINT ON SHOULDER TO HEM) BACK	66	71	73.5	76	79	79	81	84
---	----	----	------	----	----	----	----	----