

Specifications for BMP51/53 Labelmaker Labels

Adhesive	Permanent Acrylic
Article No.	143346
Brady Material No.	B-499
Material Type	Nylon Cloth
Colour	Black on Yellow
Finish	Matt
Order Reference	M-82-499-YL-BK
Printer Compatibility	BMP41; BMP51; BMP53
Size - Diameter	9.53
Additional Information	Low profile; High adhesion
Thickness (mm)	0.166
Total Qty per Pack	240 Label(s) / Box
Approval/Compliance	UL Recognised; CSA Accepted; Halogen Free (DIN VDE 0472/part 815)
Application	Laboratory Identification
Environment	Freezer; Liquid Nitrogen; Autoclave
Industry	Healthcare; Laboratory
Laboratory Application	Centrifuge & PCR Tubes;Cryo Tubes
Description	Nylon cloth with permanent adhesive allows labelling in environments with heat, cold, oil and dirt. Ideal for wire and cable marking, electronic component marking, laboratory vial identification and general labelling. Please Note: This material is UL recognized with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.
Max. Service Temp. °C	90
Min. Service Temp. °C	-40
Shape	Circle
Software	LabelMark
Surface	For smooth, textured/rough or Highly textured/Low surface energy surfaces
Vial/Tube (ml)	0.5 - 1.5 ml