

## E-15 Cassiopeia



### Technical Specs

#### Technical Specifications of the Cassiopeia E-15

**Model** E-15

**Display** 240 x 320, Bright Back-lit, FSTN liquid crystal, 16 Level Gray-Scale

**CPU** 69 MHz

**Interface** Serial: RS232C, IrDA 1.0 (115.2bps max.)

**Memory** 16MB RAM, 16MB ROM

**Built-in**

- Type I/II (3.3V) CompactFlash Slot

- Microphone

- Speaker

- Earphone Jack

- Flashing Alarm Indicator

- **Power** - Alkaline AAx2 or NiMH Rechargeable battery-- Shortened by use of CompactFlash card, modem and Backlight

- Back-up Lithium CR2032 (Approximately 5 years)

- AC Adapter AD-C50200U for direct power and recharge the NiMH battery

- Action Control Wheel for one-handed data access

**Weight** 6.5 oz (excluding batteries)

**Size** Height 5/8" x Width 3 1/4" x Depth 5"

### **System Requirements**

- **Operating System Requirements** Windows 95/98 (US) or Windows NT Workstation 4.0
- **Processor Requirements** 486/33DX or higher, Pentium 90 recommended for Windows 95, Pentium recommended for Windows NT
- **RAM Requirements** 16MB for Windows NT (32 MB recommended) 16MB for Windows 95
- **Hard Disk Requirements** 10MB to 50MB
- **Communication Port Available** 9 pin or 25 pin with adapter
- **CD ROM Drive**
- **VGA Graphic card** Super VGA 256 color recommended
- **Keyboard with mouse**