

Han A Base Panel for Central Lever



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 032 0381
Specification	Han A Base Panel for Central Lever
HARTING eCatalogue	https://harting.com/09200320381

Identification

Category	Hoods / Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Bulkhead mounted housing
Type	Low construction

Version

Size	32 A
Locking type	Central locking lever (on the hood)
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Tightening torque	1 Nm Fixing screws M4
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	1
Net weight	94.32 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140040151
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466