

# Product Information



## 5520PJI050L51-8

EAN 4031582338676

Swivel castor, housing made of Polyamide, with blind hole for furniture fittings.

Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing

Technical Data	
Wheel diameter	50 mm
Width of Tread	10 mm
Castor width	54 mm
Centre hole	8 mm
Swivel Interference	96 mm
Overall height	56 mm
Temperature	- 10 / + 40 °C
Standard	EN 12528
Swivel Radius	48 mm
Hardness of tread	A 87 Shore
Load capacity	40 kg
Load capacity (static)	80 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

# Product Information



## 5520PJI050L51-8

EAN 4031582338676

