

18V Pole Saw LXT®, DUA200

200 mm

Model DUA200 is a 200 mm pole saw powered by an 18V LXT Li-Ion battery

This model has enough power for users to perform tasks. Equipped with a brushless motor this tool reduces the burden during operation and improves the ease of targeting branches, as a result to its lightweight tool head and high work efficiency



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Chain Speed (No Load)	6,7 m/s
Chain Pitch	0,325 "
Chain Gauge	0,043 "
Chain Gauge	1,1 mm
Number of Drive Links	38
Brushless Motor	✓
chain bar length	200 mm (8")
Vibration Level (3 axes) at Front Handle	$\leq 2,5 \text{ m/s}^2$
Vibration Level (3 axes) at Rear Handle	$\leq 2,5 \text{ m/s}^2$
Vibration Uncertainty (K Factor)	$1,5 \text{ m/s}^2$
Sound Power Level (L_{WA})	87 dB(A)
Sound Pressure Level (L_{pA})	79 dB(A)

User benefits

- Automatic chain lubrication
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing