

Eaton 185954

Catalog Number: 185954

Eaton Moeller® series C30 Indicator light, Flat, Cable (black) with non-terminated end, 4 pole, 1 m, Lens green, LED green, 24 V AC/DC

General specifications



Product Name	Catalog Number
Eaton Moeller® series C30 Indicator light	185954
EAN	Product Length/Depth
4015081814558	1060 mm
Product Height	Product Width
46 mm	36 mm
Product Weight	Certifications
0.063 kg	IEC/EN 60947-5-1
	VDE 0660

Product specifications

Type

Indicator lights

Product Category

RMQ compact solution

Electric connection type

Other

Fitted with:

Light source

Front ring

Pollution degree

3

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Connection to SmartWire-DT

No

Rated impulse withstand voltage (Uimp)

800 V AC

Bezel color

Chrome

Cable material

PUR

Lamp socket type

LED

Actuator diameter

4.7 mm

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Number of pilot lights

1

Opening diameter

30 mm

Opening height

0 mm

Resources

Catalogs

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004135.pdf](#)

[DA-DC-00004157.pdf](#)

Drawings

[eaton-operating-c30-indicator-light-dimensions-002.eps](#)

[eaton-operating-c30-indicator-light-3d-drawing-002.eps](#)

[eaton-operating-button-symbol-004.eps](#)

eCAD model

[DA-CE-ETN.C30C-FL-G-24-P62](#)

Installation instructions

[IL047021ZU](#)

Installation videos

[Eaton's RMQ compact solution pilot devices](#)

mCAD model

[DA-CD-c30_1_open_cable](#)

[DA-CS-c30_1_open_cable](#)

Sales notes

[eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf](#)

System overview

[Pilot devices - selection aid](#)

Wiring diagrams

[eaton-operating-c22-indicator-light-wiring-diagram-003.eps](#)

Rated insulation voltage (Ui)

30 V

Rated operational voltage (Ue) - max

24 V

Bezel material

Metal

Degree of protection

IP Other

NEMA Other

Lens color

Green

Voltage type

AC/DC

Design

Cable end open

Flat

Mounting position

As required

Light color

Green

Rated conditional short-circuit current (Iq)

1 kA

Rated operational voltage (Ue) - min

24 V

Width opening

0 mm

Overvoltage category

III

Cable length

1 m

Connection type

Cable (black) with non-terminated end, 4 pole

Lens type

Flat

Round

Shock resistance

30 g, Mechanical, Shock duration 11 ms

Rated operational voltage

24 V AC/DC (LED)

Short-circuit protection rating

Max. 4 A gG/gL, Fuse, Contacts

Tightening torque

2 Nm, Threaded ring



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia